

Terminal Boxes

Steel Range

Stainless steel terminal box | SSTB

IP 66 | TYPE 4X, 12, 13 | IK 08



Material:

AISI 304 pre-grained stainless steel / AISI 316L (on request). Body: 1 mm. Cover: 1.5 mm.

Body:

Folded and seam welded. Four M6x13 studs for bottom profile / mounting plate fixation.

Gasket:

For AISI 316L, sealing is ensured by an injected one piece silicone gasket.

Earthing:

M8x18 mm earthing studs in body and cover, M8 nuts, earthing washers and earthing labels.

Protection:

IP 66 | TYPE 4X, 12, 13 | IK 08.

Finish:

240s pre-grained stainless steel (average 0.5 micron).

Approvals:

CE, GOST, Kema Keur - DEKRA, cULus_UL Listed.

Delivery:

Body, cover, cover screws, fixing screws, cover plugs and earthing facilities.



IP 66 | TYPE 4X, 12, 13 | IK 08

Box dimension			Item no.
H	W	D	
150	150	80	SSTB151508
150	150	80	SSTB151508-316
150	150	120	SSTB151512
150	150	120	SSTB151512-316
150	300	80	SSTB153008
150	300	80	SSTB153008-316
150	300	120	SSTB153012
150	300	120	SSTB153012-316
200	200	80	SSTB202008
200	200	80	SSTB202008-316
200	200	120	SSTB202012
200	200	120	SSTB202012-316
200	300	80	SSTB203008
200	300	80	SSTB203008-316
200	300	120	SSTB203012
200	300	120	SSTB203012-316
200	400	80	SSTB204008
200	400	80	SSTB204008-316
200	400	120	SSTB204012
200	400	120	SSTB204012-316
200	500	120	SSTB205012

Box dimension			Item no.
H	W	D	
200	500	120	SSTB205012-316
200	600	120	SSTB206012
200	600	120	SSTB206012-316
200	800	120	SSTB208012
200	800	120	SSTB208012-316
300	300	80	SSTB303008
300	300	80	SSTB303008-316
300	300	120	SSTB303012
300	300	120	SSTB303012-316
300	400	120	SSTB304012
300	400	120	SSTB304012-316
300	500	120	SSTB305012
300	500	120	SSTB305012-316
300	600	120	SSTB306012
300	600	120	SSTB306012-316
400	400	120	SSTB404012
400	400	120	SSTB404012-316
400	600	120	SSTB406012
400	600	120	SSTB406012-316
400	800	120	SSTB408012
400	800	120	SSTB408012-316

Dimensional drawing | SSTB

