

Monitor/keyboard unit

Accessories

Monitor/keyboard unit, 1 U with 17" TFT display and VGA/DVI connection

Benefits:

- With digital and analog interfaces, VGA, DVI-D, PS/2, USB
- Simple, one-man installation
- Optionally with integrated KVM switch for up to 8 servers

Technical design:

- 432 mm/17" TFT display
- Physical resolution: 1280 x 1024
- Format: 4 : 3
- Colours: 16.7 million
- Brightness: approx. 350 cd/m² (typ.)
- Contrast ratio: approx. 1000 : 1
- Mains voltage: 100 – 240 V/50 – 60 Hz
- Ambient temperature: +5°C...+45°C (operation)
- Max. power consumption in operation, without optional KVM system: 32 W
- Max. power consumption with closed monitor unit, without optional KVM system: < 1 W
- Rear connections:
Mains voltage, VGA, DVI, PS/2, USB,
power supply for KVM
- Lockable at the front
- Cables are safely routed in the energy chain



Accessories:

- For monitoring several servers:
KVM switch, see page 461

Width	Height U	Depth mm	Installation depth mm	Packs of	Colour	Keyboard	Model No.
482.6 mm/ 19"	1	680	680 – 850	1 pc(s).	RAL 7035	German	9055.310
						English	9055.312
					RAL 9005	German	9055.410
						English	9055.412



KVM switch

SSC view 8 USB

For rear attachment on the monitor/keyboard unit. The SSC view 8 USB may be operated with up to 8 servers. It is operated via the monitor/keyboard unit with an OSD menu or hotkeys.

Technical specifications:

- Server/console connections
Video: VGA/HD15
Keyboard/mouse: PS/2 or USB
- Max. video resolution: 1280 x 1024 at 85 Hz
- Bandwidth: 200 MHz
- Power consumption: 10 W
- W x H x D: 482.6 x 44 x 140 mm
- Voltage supply: 12 V (DC) via MTE

Protection category IP to IEC 60 529:

- IP 20

Colour:

- RAL 9006

	Packs of	Model No.
SSC view 8 USB	1 pc(s).	7552.002

Connection cable for server/VGA	Length m	Packs of	Model No.
PS/2	2	1 pc(s).	7552.120
PS/2	4	1 pc(s).	7552.140
USB	2	1 pc(s).	7552.122
USB	5	1 pc(s).	7552.142



Also required:

- Monitor/keyboard unit, see page 461

