

Support arm system CP 40/60/120/180

Pivot

with/without jib

- For direct, vertically hinged integration into machines and systems
- Enclosure suspended or top-mounted
- With integral rotation range restrictor
- To fit enclosures with mounting cut-out Ø 130 mm

Jib length mm	Colour RAL	Load capacity N	Model No.
–	7024	700	6016.700
200	7024/7035	700	6016.600

Technical details:

Available on the Internet



Tilting adaptor +/-45°

for command panels with support arm connection Ø 130 mm

For mounting between:

- Coupling CP 60, 6206.300
 - Coupling CP 120, 6212.300
- or
- Mounting bracket CP 60, 6206.320
 - Mounting bracket CP 120, 6212.320
- or
- Angle coupling 90°, CP 60, 6206.380
 - Angle coupling 90°, CP 120, 6212.380
- and the command panel

Tilt angle:

- Adjustable in 7.5° increments

Material:

- Tilting adaptor: Cast aluminium
- Concertina section: Plastic

Colour:

- Tilting adaptor: RAL 7035
- Concertina section: RAL 7024

Supply includes:

- Seals
- Concertina section
- Assembly parts

Weight kg	Model No.
1.2	6206.420

Technical details:

Available on the Internet

