

NH slimline switch-disconnectors

Size 1 – 2, design 3-pole, switchable

Size	Packs of	1	1	2	Page
Rated operating current max. A		250	250	400	
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	
Installation type		Screw attachment	Screw attachment	Screw attachment	
Cable outlet		Bottom	Top	Bottom	
Type of connection		Bolt M12	Bolt M12	Bolt M12	
Connection of round conductors mm ²		6 - 240	6 - 240	6 - 240	
Width mm		100	100	100	
Height mm		772	772	772	
For converter installation		–	–	–	
For bar systems with centre-to-centre spacing mm		185	185	185	
For bar thickness mm		10	10	10	
Model No.	1 pc(s).	9677.160	9677.165	9677.260	
Accessories					
Connection space cover	1 pc(s).	9677.410	9677.410	9677.410	115
Connection space cover, rear	1 pc(s).	9677.412	9677.412	9677.412	115
Clamp-type terminal		–	–	–	115
Box terminal		see page	see page	see page	115
Contact terminal	3 pc(s).	9677.485	9677.485	9677.485	116
Micro-switch	1 pc(s).	9677.418	9677.418	9677.418	116
Current converter		–	–	–	116

Size 2 – 3, design 3-pole, switchable

Size	Packs of	2	3	3	Page
Rated operating current max. A		400	630	630	
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	
Installation type		Screw attachment	Screw attachment	Screw attachment	
Cable outlet		Top	Bottom	Top	
Type of connection		Bolt M12	Bolt M12	Bolt M12	
Connection of round conductors mm ²		6 - 240	6 - 240	6 - 240	
Width mm		100	100	100	
Height mm		772	772	772	
For converter installation		–	–	–	
For bar systems with centre-to-centre spacing mm		185	185	185	
For bar thickness mm		10	10	10	
Model No.	1 pc(s).	9677.265	9677.360	9677.365	
Accessories					
Connection space cover	1 pc(s).	9677.410	9677.410	9677.410	115
Connection space cover, rear	1 pc(s).	9677.412	9677.412	9677.412	115
Clamp-type terminal		–	–	–	115
Box terminal		see page	see page	see page	115
Contact terminal	3 pc(s).	9677.485	9677.485	9677.485	116
Micro-switch	1 pc(s).	9677.418	9677.418	9677.418	116
Current converter		–	–	–	116