

**AF25 Light CLASSIC**

Three row bar 75x75

Grid (A) 25, hole diameter 12,5mm

Nr.	B	g
24882	100	343
25075	150	514
25376	200	686
22617	250	857
25076	300	1.029
26002	350	1.200
27412	400	1.372
25078	450	1.543
22618	500	1.715
33091	550	1.886
33090	600	2.057
32352	650	2.229
33041	700	2.400
22619	750	2.572
31538	800	2.743
32350	850	2.915
27223	900	3.086
26894	950	3.258
22621	1000	3.429
33551	1050	3.600
25080	1100	3.772
29685	1150	3.943
30751	1200	4.115
22623	1250	4.286
27855	1300	4.458
33050	1350	4.629
33060	1400	4.801
33552	1450	4.972
22624	1500	5.144
33290	1600	5.486
33089	1700	5.829
33291	1800	6.172
33292	1900	6.515
22771	2000	6.858

**AF40 Light CLASSIC**

Three row bar 120x120

Grid (A) 40, hole diameter 20mm

Nr.	B	g
24950	160	1.404
25123	200	1.755
24951	240	2.106
24827	280	2.457
24952	320	2.808
25122	360	3.159
23574	400	3.510
25735	440	3.861
24931	480	4.212
26008	520	4.563
25121	560	4.914
25124	600	5.265
25736	640	5.616
27458	680	5.967
24930	720	6.318
24828	760	6.669
23575	800	7.020
25029	840	7.371
25843	880	7.722
27597	920	8.073
24929	960	8.424
27435	1000	8.775
25028	1080	9.477
27169	1160	10.179
23576	1200	10.530
27601	1280	11.232
26892	1360	11.934
24953	1400	12.285
24829	1480	12.987
25310	1560	13.689
23577	1600	14.040
25950	1680	14.742
29918	1760	15.444
25737	1800	15.795
27538	1880	16.497
23578	2000	17.550
27602	2200	19.305

**AF50 Light CLASSIC**

Three row bar 150x150

Grid (A) 50, hole diameter 25mm

Nr.	B	g
28123	100	1.389
28124	150	2.083
28125	200	2.777
27521	250	3.472
26817	300	4.166
28126	350	4.860
28127	400	5.554
27854	450	6.249
26978	500	6.943
33302	600	8.332
27522	700	9.720
29366	800	11.109
27853	900	12.497
26979	1000	13.886
33303	1100	15.275
33304	1200	16.663
29805	1300	18.052
29699	1400	19.440
26981	1500	20.829
33305	1600	22.218
28557	1700	23.606
27606	1800	24.995
33306	1900	26.383
26983	2000	27.772
26985	2500	34.715
26987	3000	41.658
26989	3500	48.601
26991	4000	55.544
26993	4500	62.487
26995	5000	69.430
26997	5500	76.373
26999	6000	83.316



**ALUFIX CLASSIC** bars can be anodized in different colours. The colour natural is standard, black (-1) is available as an alternative. Other colours on request

**i** Other dimensions on request