

















Support arm system CP 120

	Rotating/tilting	Rigid	Length mm	Weight kg	Colour RAL	Enclosure section CP 120	Enclosure section CP 120/60	Desk section CP 120	Wall section CP 120	
						Model No.				
Adaptor CP 120/60 from support arm connection Ø 130 mm to □ 120 x 65 mm										
	see page 157	–	■	–	0.5	7035	6212.500	6212.500	–	–
Attachment CP 120/60 for support arm connection										
	Ø 130 mm	–	■	–	0.7	7035	6212.320	6206.320	–	–
	□ 120 x 65 mm	–	■	–	0.7	7035	–	6206.360	–	–
Coupling CP 120/60 for support arm connection										
	Ø 130 mm	■	–	–	2.0	7035	6212.300	6206.300	–	–
	□ 120 x 65 mm	–	–	–	–	–	–	6206.340	–	–
Angle coupling 90° CP 120 for support arm connection										
	Ø 130 mm	■	–	–	2.1	7035/ 7024	6212.380	–	–	–
Support section CP 120/60										
		–	–	250	2.0	7035	CP 120	CP 60 ¹⁾	CP 120	CP 120
Solid	–	–	500	3.9	6212.025		6206.025	6212.025	6212.025	
	–	–	1000	7.8	6212.100		6206.100	6212.100	6212.100	
	–	–	2000	15.6	6212.200		6206.200	6212.200	6212.200	
	Open	–	–	500	4.6	7035/ 7024	6212.150	–	6212.150	6212.150
		–	–	1000	9.2		6212.110	–	6212.110	6212.110
		–	–	2000	18.4		6212.210	–	6212.210	6212.210
Adaptor for support arm combination CP 120/60										
	see page 159	–	■	–	0.7	7035	–	6212.640	–	–
Angle piece 90°, CP 120										
		–	■	–	1.1	7035/ 7024	6212.600	–	–	6212.600
Intermediate hinge CP 120										
		■	–	–	4.4	7035/ 7024	–	–	6212.620	–
Top-mounted joint CP 120										
	Vertical outlet	■	–	–	3.8	7035	–	–	–	6212.720
	Horizontal outlet	■	–	–	4.3	7035/ 7024	–	–	–	6212.700
Wall-mounted hinge CP 120										
	Vertical outlet	■	–	–	5.5	7035/ 7024	–	–	–	6212.760
	Horizontal outlet	■	–	–	6.1	7035/ 7024	–	–	–	6212.740
Wall/base mounting bracket CP 120, small										
		–	■	–	0.5	7035	–	–	–	6212.820
Wall/base mounting bracket CP 120, large										
		–	■	–	2.5	7035/ 7024	–	–	–	6212.800
Mounting component CP 120/180 for signal pillar										
	see page 720	–	■	–	0.1	7024	6212.900	6212.900	6212.900	6212.900
Tilting adaptor										
For support arm connection Ø 130 mm and □ 120 x 65 mm									see page 147	
Accessories										
Adaptor CP 120 to support arm, height-adjustable 6071.600									see page 159	

¹⁾ Weight information and diagrams for CP 60, see page 147