



Standard Blindniet ALFO® Serie 10.708





Edelstahl A2 / Edelstahl A2/A3



[1.4301]

> Flachkopf
> offen



DIN EN ISO 15983

d	l +1		Nr.	
2,4	6,0	0,5 - 3,5	10.708.024.060	500
	d_k 5,0 ±0,2	d_m 1,5	k 0,8 ±0,1	2,5 mm
3,0	6,0	0,5 - 3,0	10.708.030.060	500
	8,0	3,0 - 5,0	10.708.030.080	500
	10,0	5,0 - 7,0	10.708.030.100	500
	12,0	6,5 - 8,5	10.708.030.120	500
	16,0	8,5 - 12,0	10.708.030.160	500
d_k 6,3 -0,7	d_m 1,9	k 0,8 ±0,2	3,1 mm	2050 N
3,2	4,0	0,5 - 1,5	10.708.032.040	500
	6,0	0,5 - 3,0	10.708.032.060	500
	8,0	3,0 - 5,0	10.708.032.080	500
	10,0	5,0 - 7,0	10.708.032.100	500
	12,0	6,5 - 8,5	10.708.032.120	500
	16,0	8,5 - 12,0	10.708.032.160	500
d_k 6,5 -0,7	d_m 1,9	k 0,8 ±0,2	3,3 mm	2050 N
4,0	6,0	1,0 - 2,5	10.708.040.060	500
	8,0	2,5 - 4,5	10.708.040.080	500
	10,0	4,5 - 6,5	10.708.040.100	500
	12,0	6,5 - 8,5	10.708.040.120	500
	14,0	8,5 - 10,5	10.708.040.140	500
	16,0	10,0 - 12,0	10.708.040.160	500
	18,0	12,0 - 14,0	10.708.040.180	500
	20,0	14,0 - 16,0	10.708.040.200	500
d_k 8,0 -1,0	d_m 2,5	k 1,0 ±0,3	4,1 mm	2750 N

Die hammerförmige Ausprägung des Dornkopfes sorgt für eine optimale Schließkopfbildung.



d	l +1		Nr.	
4,8	8,0	1,5 - 4,0	10.708.048.080	500
	10,0	4,0 - 6,0	10.708.048.100	500
	12,0	6,0 - 8,0	10.708.048.120	500
	14,0	7,0 - 9,5	10.708.048.140	500
	16,0	8,0 - 11,0	10.708.048.160	500
	18,0	11,0 - 13,0	10.708.048.180	500
d_k 9,5 -1,0	d_m 2,9	k 1,1 ±0,3	4,9 mm	4250 N
5,0	8,0	2,0 - 4,0	10.708.050.080	500
	10,0	4,0 - 6,0	10.708.050.100	500
	12,0	6,0 - 8,0	10.708.050.120	500
	14,0	7,0 - 9,5	10.708.050.140	500
	16,0	8,0 - 11,0	10.708.050.160	500
	18,0	11,0 - 13,0	10.708.050.180	500
	20,0	13,0 - 15,0	10.708.050.200	500
	25,0	15,0 - 20,0	10.708.050.250	250
	30,0	20,0 - 25,0	10.708.050.300	250
	35,0	25,0 - 30,0	10.708.050.350	250
	40,0	30,0 - 35,0	10.708.050.400	250
d_k 9,5 -0,8	d_m 2,9	k 1,1 ±0,3	5,1 mm	4700 N
6,0	10,0	2,0 - 5,5	10.708.060.100	250
	12,0	5,5 - 7,5	10.708.060.120	250
	16,0	7,5 - 11,0	10.708.060.160	250
d_k 12,0 -1,2	d_m 3,8	k 1,5 ±0,4	6,1 mm	5700 N
6,4	10,0	2,5 - 6,0	10.708.064.100	250
	12,0	4,0 - 7,5	10.708.064.120	250
	14,0	6,0 - 9,5	10.708.064.140	250
	16,0	7,5 - 11,5	10.708.064.160	250
	18,0	9,0 - 13,0	10.708.064.180	250
	20,0	12,0 - 14,0	10.708.064.200	250
	25,0	14,0 - 19,0	10.708.064.250	250
d_k 13,0 -1,5	d_m 3,8	k 1,8 ±0,4	6,5 mm	6500 N

Durchmesser 6,0 und 6,4 mm nicht genormt.