



System accessories Page 507 **Comfort Panel** Page 124 **Optipanel** Page 126 **TFT monitor** Page 706

Compact enclosure, ready to connect. Standard commercially available tower PCs, up to W/H/D: 250 x 530 x 600 mm (max. 20 kg) may be attached securely to the base screw fastened to the door using the retaining strap supplied loose. The rear interfaces of the PC are readily accessible with the door open. Because the socket strip and fan-and-filter unit are already pre-installed, the enclosure is ready for immediate use.

Roof prepared for mounting

- worktop
- beneath surfaces

Base prepared for mounting

- cast feet
- on surfaces

Material:

- Enclosure: Sheet steel
- Door: Sheet steel
- Design strips: Aluminium

Surface finish:

- Enclosure: Powder-coated, textured paint
- Door: Powder-coated

Colour:

- Enclosure: RAL 7035
- Door: RAL 7015
- Design strips: RAL 7035

Protection category IP to IEC 60 529:

- IP 54 in conjunction with connector gland supplied loose

Protection category NEMA:

- NEMA 12 in conjunction with connector gland supplied loose

Supply includes:

- Enclosure of all-round solid construction
- R/h door hinge
- Door with base screw-fastened on the inside
- Side cam lock
- Rear panel with two cut-outs for use of the connector gland supplied loose
- Cable gland M20, brass, nickel-plated
- Outlet filter fitted in left side panel
- Fan-and-filter unit fitted in right side panel
- Door-operated switch, supply socket for 230 V power supply, socket strip with 3 sockets and overvoltage protection

Please note the product-specific scope of supply.

Enclosure for tower PC

Width mm	Packs of	760	Page
Height mm		760	
Depth mm		300	
Model No.	1 pc(s).	6900.300	
Weight kg		55.0	
Also required			
Connection cable	5 pc(s).	4315.100	639
Accessories			
Cast feet	2 pc(s).	6902.920	519
Twin castors	1 set(s)	7495.000	522
Worktop	1 pc(s).	6902.310	165
Optipanel	1 pc(s).	6380.040	126
TFT monitor	1 pc(s).	6450.020	706
TopTherm fan-and-filter units		from page	316
Lock systems		from page	561