


## SERIES 65



### “TR” POLYURETHANE WHEELS, ALUMINIUM CENTRE, SWIVEL TOP PLATE BRACKET TYPE “EP” WITH BRAKE

#### Wheel description




**Tread:** “TR” polyurethane, hardness 93 +/- 5 Shore A, excellent rolling resistance and elasticity, good resistance to wear and to tearing.

**Centre:** aluminium.

**Hub:** the housing is obtained by moulding and contains ball bearings series Z.

#### Bracket description

##### Standard duty bracket type EP (max. carrying capacity 1600 daN)



1) **Plate:** green galvanised steel plate

2) **Fork:** green galvanised steel plate

4) **King pin:** solid with the machined plate

5) **Swivel actions:** axial ball bearing anche tapered roller bearing


6) **Dust seal:** orange polyethylene

**Finishing:** white galvanisation

**Fitting:** top plate

#### Brake description

##### Adjustable rear-locking brake



Double-action rear brake that locks the wheel and the castor at the same time. The brake is efficient and easy to use: a simple top-to-bottom movement using the tip of the foot on two independent pedals is all that's needed to engage and release the lock quickly and smoothly. Locking force can be adjusted using an M8 socket screw.